

specifications

1.3 HP Models

Vacuum Motor:

120 Volt, 2 Stage By-Pass;

94 CFM - Waterlift 84"

Current: 7.5 AMPS

Sound Level: 78dB

Power Cord:

30 Ft, 18/3 Wire Grounded

Safety Yellow

1010DAF Dry (394572)

Steel Tank Recovery Capacity:

7 Gallon Wet / .90 Bushel Dry

1010SSDAF Dry (309958)

SS Tank Recovery Capacity:

7 Gallon Wet / .90 Bushel Dry

1510DAF Dry (395943)

Steel Tank Recovery Capacity:

12 Gallon Wet / 1.60 Bushel Dry

2.3 HP Models

Vacuum Motor:

120 Volt, 2 Stage By-Pass;

115 CFM - Waterlift 110"

Current: 11.0 AMPS

Sound Level: 77dB

Power Cord:

30 Ft, 14/3 Wire Grounded

Safety Yellow

1515DAF Dry (395951)

Steel Tank Recovery Capacity:

12 Gallon Wet / 1.60 Bushel Dry

2015DAF Dry (380431)

Steel Tank Recovery Capacity:

16 Gallon Wet / 2.00 Bushel Dry

2015SSDAF Dry (396133)

SS Tank Recovery Capacity:

16 Gallon Wet / 2.00 Bushel Dry



Optional Wet Conversion Kit

Converts a steel HEPA dry vacuum over to a wet vacuum for removal of liquids.



1010DAF



1010SSDAF



1510SSDAF

Steel and Stainless Steel Dry

Our hazardous waste Vacuums with HEPA filtration are designed for the removal of mold, ceramic dust, aluminum, fiberglass and many other hazardous materials.

Designed for use in clean rooms, hospitals and industrial plants or wherever air and dust pollutants exist.

Equipped with the HEPA filter system, consisting of a certified absolute filter, double layer intermediary micro filter and totally enclosed 2 ply disposable paper filter bag.

Push Handle

Chrome plated steel on glidemobile style vacuums.

Holddown Clamps

Chrome plated spring steel with non-marring tips to ensure a positive vacuum seal.

Cold Rolled Steel and Stainless Steel Tanks

Reinforced ribs strengthen tanks for handling higher waterlift. Double roll over bottom seal prevents leaking.

8" Rear Wheels

On glidemobile style vacuums.

HEPA Filter System

Large HEPA Filter

Rated with a minimum efficiency of 99.97% @ 0.3 microns. Tested using the HOT DOP method @ 100 CFM.

2 Ply Intermediate Filter

For protection and extended life of the HEPA filter.

Microply™ 2 Ply Disposable Paper Filter Bag

Extra Large Totally Enclosed for greater filtration area.